
THE ULTIMATE X-RAY SOLUTION







PORTABLE X-RAY SYSTEMS

Digital Radiography Solutions for NDT Applications



X-RAY SYSTEMS

X-RAY GENERATOR, DETECTOR, AND SOFTWARE IN ONE BUNDLE!

Discover our complete range of portable X-ray systems for NDT inspections.


Fully developed in-house, these packages combine a detector, an X-ray generator, and Sherlock NDT, a state-of-the-art and user-friendly NDT inspection software.

Paired with Teledyne ICM's X-Ray generators (**CP Series** or **CP Batteries**), the **GO-SCAN**'s detectors deliver a sharp, clear, and detailed image and can reveal a very large majority of defects such as cracks, corrosion and failing welds.

Sherlock NDT, Teledyne ICM's NDT inspection software is fully compatible with Teledyne ICM's complete range of portable X-ray generators. It is the perfect tool for industrial radiography, allowing compliancy with most quality standards. The intuitive and user friendly touchscreen software produces high quality images, allows real-time (video) acquisition, and comes with many different enhancement features.

Make your own selection according to your inspection needs.

CONNECTIVITY





X-RAY GENERATORS: CPBATTERY OR SITEX CPSERIES












NSTANT	WIDE INPUT P
TENTIAL	RANGE

	Unit	CP120B	СР160В	SITEX CP160D	SITEX CP200D	SITEX CP200DS	SITEX CP225D	SITEX CP300D
Radiation geometry	-	Direc	tional	Directional	Directional	Directional	Directional	Directional
Power supply	-	Bat	tery	Mains	Mains	Mains	Mains	Mains
Output voltage range	kV	40 to 120	40 to 160	10 to 160	10 to 200	10 to 200	10 to 225	20 to 300
Tube current range	mA	0.1 to 1.0	0.1 to 0.5	1 to 10	1 to 10	0.5 to 10	1 to 10	1 to 10
Tube current at full output	mA	1	0.5	5.6	4.0	3.7	4.0	3
Maximum power at the anode	W	120	80	900	900	750	900	900
Constant power mode	-	Ye)S	Yes	Yes	Yes	Yes	Yes
Working cycle at 30°C (*)	%	ı	,	100	100	100	100	100
Steel penetration (**)	mm/in	10 / 0.4	21/0.8	29 / 1.14	42 / 1.65	40 / 1.57	47 / 1.9	66 / 2.6
Weight	Kg/lbs	7.0 / 15.4	9.2/20.3	14.7/30.86	14.7/30.86	15.9/35.05	14.7/30.86	26 / 57.32
Overall dimensions	mm/in	Ø 124 x 440 / 4.9 x 17.3	Ø 124 x 490 / 4.9 x 19.3	Ø 140 x 725 / 5.5 x 28.5	Ø 140 x 725 / 5.5 x 28.5	Ø 140 x 705 / 5.51 x 27.75	Ø 140 x 725 / 5.5 x 28.5	Ø 180 x 839 / 7.1 x 33
Leakage dose at 1 m at full output	mSv/h	<2.0		< 2.0	< 2.0	< 2.0	< 2.0	< 5.0
Optical focal spot according to EN 12543	mm/in	0.8 x 0.5 / 0.03 x 0.02	0.8 x 0.7 / 0.03 x 0.03	3.0 / 0.12	3.0 / 0.12	1	3.0 / 0.12	3.0 / 0.12
Maximum useful angle	0	50 x 50	60 x 60	60 x 40 elliptical	60 x 40 elliptical	60 x 40 elliptical	60 x 40 elliptical	60 x 40 elliptical
Inherent filtration	mm/in	Equiv. 3.5	/ 0.1 (AI)	0.8 / 0.03 (Be window)	0.8 / 0.03 (Be window)	0.8 / 0.03 (Be window)	0.8 / 0.03 (Be window)	0.8/ 0.03 (Be window)
Waterprooflevel	-	IP	54	IP65	IP65	IP65	IP65	IP65
Operating temperature	°C/F°	-25 to -13 to		-30 to +60 / -22 to +140	-30 to +60 / -22 to +140	-30 to +60 / -22 to +140	-30 to +60 / -22 to +140	-30 to +60 / -22 to +140
Storagetemperature	°C/F°	-40 to		-40 to +70 / -40 to +158	-40 to +70 / -40 to +158	-40 to +70 / -40 to +158	-40 to +70 / -40 to +158	-40 to +70 / -40 to +158
Guard rings	-			2	2	2	2	2

^(*) Open air - airstream 5m/sec.

(**) 700 mm FFD, 10 min , AA400, D=2 for CPD



X-RAY DETECTORS: GO-SCAN SERIES











	Unit	GO-SCAN 1510 HR	GO-SCAN 1510 XR	GO-SCAN 3025	GO-SCAN 4335	
GENERAL						
Technology	-	CMOS Active Pixel	CMOS Active Pixel	aSi	aSi	
Pixel pitch	μm	99	49.5	120	154	
Sensitivity settings	#	2	1	1	1	
Active area	mm/in	102 x 153 / 4 x 6	102 x 153 / 4 x 6 114 x 145 / 4.5 x 5.7 300 x 250 / 11.8 x 9.8		434 x 355 / 16.9 x 13.8	
Active resolution	pxl	1032 x 1548	2304 x 2940	2560x 2048	2816 x 2304	
BANDWITH						
Data interface	-	GigE & Wi-Fi	GigE & Wi-Fi GigE & Wi-Fi GigE & Wi-Fi		GigE & Wi-Fi	
ADC conversion	bits	14	14	16	16	
Frame rate—1x1 (GigE)	fps	up to 30	up to 9	0.3	0.3	
POWER CONSUMPTION						
Power supply	-	Battery / Mains*	Battery / Mains*	Battery / Mains*	Battery / Mains*	
Power consumption	W	15	15	17	20	
Battery performance	-	Approx. 7 hours	Approx. 7 hours	Approx. 7 hours	Approx. 7 hours	
INTEGRATION						
Dimension detector head	mm/in	238 x 154 x 25 / 9.4 x 6.0 x 1.0	238 x 154 x 25 / 9.4 x 6.0 x 1.0	-	-	
Overall dimension	mm/in	238 x 154 x 80 / 9.4 x 6.0 x 3.1	238 x 154 x 80 / 9.4 x 6.0 x 3.1	339x 287 x 188 / 13.34x 11.29x 7.4	464 x 388 x 188 / 18.26 x 15.27x 7.4	
Detector head weight	Kg/lbs	1.6/3.5	1.6 / 3.5	-	-	
Overall weight	Kg/lbs	3.5/7.7	3.5/7.7	3.5/6.6	5.9 / 13	
ENVIRONMENTAL						
Operating temperature	°C/F°	-20 to 50°C / -4 to +122°F	-20 to 50°C / -4 to +122°F	-20 to 50°C / -4 to +122°F	-20 to 50°C / -4 to 122°F	
Storage temperature	°C/F°	-20 to 60°C / -4 to +140°F	-20 to 60°C / -4 to +140°F	-20 to 60°C / -4 to +140°F	-20 to 60°C / -4 to 140°F	
Humidity	% R.H.	20 to 80	20 to 80	30 to 75	30 to 75	
X-ray energy range	kV	Up to 300	Up to 300	Up to 300	Up to 300	

(*) with Power/Com Cable accessory

RUGGEDIZED TABLET WITH SHERLOCK NDT SOFTWARE







PLUG AND PLAY



IMAGE EDITING



TELEDYNE FILTER

SOFTWARE FEATURES

All-in-one touchscreen software

Available in 20 languages

Add unlimited users

Library to store all inspections efficiently

Interconnected by cable or wireless

Fast image acquisition

Preset exposure configurations

MULTIPLE IMAGE EDITING FEATURES

Image editing

ADRC dynamic filter

Local contrast enhancement

Teledyne filter

Histogram equalization

DICONDE Compliant

Emboss

Black & white

Pseudo-colours

Smart measurement tool

SNR

Greyscale feature

Stitching

iSRb / automatic IQI recognition

Annotation / Highlight

Mirroring / Rotation

Pixel map edition

Real-time Image acquisition

Exposure time calculator

Wall thickness measurement

 $Monitoring \ and \ modifying \ parameters \ during \ inspection$

During the inspection, possibility to adapt parameters and apply filters

Superpower Zoom (up to 500%)

Drag&drop external images from Windows into the image editor

Automatic file export




Stitching of multiple images



iSRb calculation and automatic IQI recognition



Wall thickness measurement



Without Teledyne Filter

With Teledyne Filter

PORTABLE X-RAY SYSTEMS Digital Radiography Solutions for NDT Applications

injury or property damage if they are used, operated, maintained, stored or disposed of improperly. In particular, the Goods may emit x-ray minimize exposure. At a minimum, Buyer should adhere to the ALARA (as low as reasonably achievable) principle and should comply with all

TELEDYNE ICMEverywhere**you**look**